

Product data sheet

Characteristics

MDECLGML150100

Clipsal - Cable Management, CA Series, GRP
Cable Ladder, 150mm Wide X 100mm Height
X 6M



Main

Product brand	Clipsal
Range of product	Series A

Complementary

Type of rung	Flat
Fixing mode	By nut By bolt
Height	100 mm
Width	150 mm
Length	6 m
Practical load capacity	735.49 N
Material	Glass reinforced plastic



Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	15 cm
Package 1 Length	10 cm
Package 1 Weight	20 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations