

## Product data sheet

### Characteristics

# MDECLGML300100

## CA Series, Clipsal - Cable Management, GRP Cable Ladder, 300mm Wide X 100mm Height X 6M



### Main

Product brand	Clipsal
Range of product	Series A

### Complementary

Type of rung	Flat
Fixing mode	By bolt By nut
Height	100 mm
Width	300 mm
Length	6 m
Practical load capacity	735.49 N
Material	Glass reinforced plastic



### Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------



### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	30 cm
Package 1 Length	10 cm
Package 1 Weight	17 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

---