

Product data sheet

Characteristics

MDECLGNL300150

Cb Cable Ladder, Clipsal - Cable Management, 300mm Wide, 6M



Main

Product brand	Clipsal
Range of product	Series B

Complementary

Type of rung	Flat
Fixing mode	By nut By bolt
Height	150 mm
Width	300 mm
Length	6 m
Practical load capacity	1098.34 N
Material	Glass reinforced plastic

Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	30 cm
Package 1 Length	15 cm
Package 1 Weight	1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

