

Product data sheet

Characteristics

MDECLGNL450150

Clipsal - Cable Management, Cb Cable Ladder, 450mm Wide, 6M



Main

Product brand	Clipsal
Range of product	Series B

Complementary

Type of rung	Flat
Fixing mode	By nut By bolt
Height	150 mm
Width	450 mm
Length	6 m
Practical load capacity	1098.34 N
Material	Glass reinforced plastic

Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile