

Product data sheet

Characteristics

MDECLGNL600150

Clipsal - Cable Management, Cb Cable Ladder, 600mm Wide, 6M



Main

Product brand	Clipsal
Range of product	Series B

Complementary

Type of rung	Flat
Fixing mode	By bolt By nut
Height	150 mm
Width	600 mm
Length	6 m
Practical load capacity	1098.34 N
Material	Glass reinforced plastic

Environment



Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	60 cm
Package 1 Length	15 cm
Package 1 Weight	1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
