

Product data sheet

Characteristics

MDECLIRGH150

GN CBL Internal 90 Degree Riser, Clipsal - Cable Management, 150mm Wide

Main

Product brand	Clipsal
---------------	---------

Complementary

Type of side joist	Flat
Type of rung	Flat
Operating angle	90 °
Width	Cable ladder: 150 mm
Material	Glass reinforced plastic

Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.