

Product data sheet

Characteristics

MDECLLDL15083

Series L GRP Cable Ladder, Clipsal - Cable Management, 150mm Wide X 83mm Height X 6M



Main

Product brand	Clipsal
Range of product	Series L

Complementary

Type of rung	Flat
Fixing mode	By nut By bolt
Height	83 mm
Width	150 mm
Length	6 m
Practical load capacity	735.49 N
Material	Glass reinforced plastic

Environment



Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	15 cm
Package 1 Length	8.3 cm
Package 1 Weight	18 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
