

## Product data sheet

### Characteristics

# MDECLLDL30083

Clipsal - Cable Management, Series L GRP  
Cable Ladder, 300mm Wide X 83mm Height X  
6M



#### Main

Product brand	Clipsal
Range of product	Series L

#### Complementary

Type of rung	Flat
Fixing mode	By bolt By nut
Height	83 mm
Width	300 mm
Length	6 m
Practical load capacity	735.49 N
Material	Glass reinforced plastic



#### Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	30 cm
Package 1 Length	8.3 cm
Package 1 Weight	10 kg

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations