

Product data sheet

Characteristics

MFINLINE-150

Clipsal, Exhaust Fan, Mixed Flow Inline, 150mm



Main

Range of product	Mixed Flow Inline Fans
Range	Mixed Flow Inline Fans
Product brand	Clipsal
Product or component type	Exhaust fan
Noise level	46 dB
Provided equipment	Dowels User manual Screws 220 mm 289 mm 148 mm
Colour	Grey

Complementary

Device mounting	Ceiling
Air flow	565 m ³ /h
Pressure	270 Pa
Power consumption in W	50 W
[In] rated current	0.22 A
Maximum revolution speed	2620 rpm
Height	247 mm
[Ue] rated operational voltage	230 V AC
Material	Polypropylene

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.7 cm
Package 1 Width	24.3 cm
Package 1 Length	30.5 cm
Package 1 Weight	3.25 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
