

Product data sheet

Characteristics

ML/ABC15DNM-WE

Medilec, Single Switch Socket Outlet, 250V, 10A, O Style, 2 Pole, Horizontal, Neon



Main

Range of product	Medilec ESP Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Height	74 mm
Width	45 mm

Environment

Standards	AS/NZS 3190 AS/NZS 3003
-----------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4 cm
Package 1 Length	7.3 cm
Package 1 Weight	57 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes