

Product data sheet

Characteristics

ML/ABC15VDNM-WE

Medilec, Single Switch Socket Outlet, 250V,
10A, O Style, 2 Pole, Vertical, Neon



Main

Range of product	Medilec ESP Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Vertical
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Height	74 mm
Width	45 mm




Environment

Standards	AS/NZS 3190 AS/NZS 3003
-----------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.3 cm
Package 1 Length	9.5 cm
Package 1 Weight	88.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes