

Product data sheet

Characteristics

ML2015/15I-WE

SOCKET SWITCHED SINGLE NEON

CIRCUIT IDENTIFICATION 15A



Main

Range of product	ML2000 Moulded Series Medilec
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Length	116 mm
Width	76 mm




Environment

Standards	AS/NZS 3112
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	96.0 g
Package 1 Height	3.4 cm
Package 1 width	8 cm
Package 1 Length	12.8 cm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration