

Product data sheet

Characteristics

ML2025-WE

Twin Switch Socket Outlet, Medilec, 250V, 10A, 2 Gang, 1 Pole

Main

Range of product	Medilec ML2000 Moulded Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	116 mm
Width	76 mm

Environment

Standards	AS/NZS 3112:approval number S/1/2025 AS/NZS 3112:approval number S/1/2015
-----------	------------------------------------------------------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	11.5 cm
Package 1 Length	7.7 cm
Package 1 Weight	113.3 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
SCIP Number	C6f2fabe-d5ba-4588-bd03-c90f7def1381
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No