

Product data sheet

Characteristics

ML2025C-BG

Medilec, Twin Switch Socket Outlet, 250V,
10A, 2 Gang, 1 Pole, Cleaner Label



Main

Range of product	ML2000 Moulded Series Medilec
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	116 mm
Width	76 mm




Environment

Standards	AS/NZS 3112 AS/NZS 3003
-----------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.1 cm
Package 1 Length	12.5 cm
Package 1 Weight	100 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes