

Product data sheet

Characteristics

ML2025C-BG

Twin Switch Socket Outlet, Medilec, 250V,
10A, 2 Gang, 1 Pole, Cleaner Label



Main

Range of product	ML2000 Moulded Series Medilec
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	116 mm
Width	76 mm

Environment

Standards	AS/NZS 3112 AS/NZS 3003
-----------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.1 cm
Package 1 Length	12.5 cm
Package 1 Weight	100 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	115 cm
Package 2 Width	85 cm

Package 2 Length	155 cm
Package 2 Weight	1.21 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations