

Product data sheet

Characteristics

ML2025RC10-WE

Medilec, RCD Protected Medilec, Twin Switch
Socket Outlet, 250V, 10A, 1 Pole, Horizontal,
10mA RCD



Main

Range of product	Medilec ML2000 Moulded Series
Product or component type	Switched socket
Product brand	Clipsal




Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Mounting Centers	84 mm
Earth-leakage protection class	Type I

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	10 cm
Package 1 Length	2 cm
Package 1 Weight	232 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12 cm
Package 2 Width	10 cm
Package 2 Length	36.8 cm
Package 2 Weight	1.282 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes