

## Product data sheet

### Characteristics

# ML2025RCD10-WE

## SWITCHED SOCKET TWIN 10A RCD 10MA



### Main

|                           |                                  |
|---------------------------|----------------------------------|
| Product or component type | Switched socket                  |
| Colour                    | White electric                   |
| Product brand             | Clipsal                          |
| Range of product          | Medilec<br>ML2000 Moulded Series |




### Complementary

|                                |                  |
|--------------------------------|------------------|
| Colour code                    | WE               |
| Control type                   | ON/OFF button    |
| Number of gangs                | 2 gangs          |
| Pin number                     | 3                |
| Number of power socket outlets | 2                |
| Actuator                       | Switch<br>Rocker |
| Mounting position              | Horizontal       |
| Fixing mode                    | By screws        |
| Local signalling               | Indicator light  |
| Material                       | Plastic          |
| Surface finish                 | Glossy           |
| [Ue] rated operational voltage | 250 V AC         |
| [In] rated current             | 10 A             |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Weight             | 205 g  |
| Package 1 Height             | 75 mm  |
| Package 1 width              | 95 mm  |
| Package 1 Length             | 120 mm |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |