

Product data sheet

Characteristics

ML2025RCD10C-BG

Medilec, Switched Socket Twin 10A RCD 10mA



Main

Range of product	Medilec ML2000 Moulded Series
Product or component type	Switched socket
Product brand	Clipsal





Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Earth-leakage protection class	Type I

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	9.6 cm
Package 1 Length	12.2 cm
Package 1 Weight	204 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes