

## Product data sheet

### Characteristics

# ML2025VI-WE

Twin Switch Socket Outlet, Medilec, 250V,  
10A, 2 Gang, 1 Pole, Vertical



### Main

Range of product	ML2000 Moulded Series Medilec
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Vertical
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	116 mm
Width	76 mm

### Environment

Standards	AS/NZS 3112:approval number S/1/2025 AS/NZS 3112:approval number S/1/2015
-----------	--

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	11.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	110.0 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>