

Product data sheet

Characteristics

ML2031RC10-WE

Residual Current Circuit Breaker, Medilec, 2 Pole, 20A, 10mA, Horizontal

Main

Product or component type	Residual current device
Product brand	Clipsal
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type I

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC
Mounting mode	Flush mounting
Size	116 x 76 mm conforming to DIN 43880
Colour	White electric
Number of gangs	1 gang

Environment

Standards	AS/NZS 3190
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	9.4 cm
Package 1 Length	12 cm
Package 1 Weight	210 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	14.0 cm
Package 2 Length	24.6 cm
Package 2 Weight	1.42 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	14.2 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes