

## Product data sheet

### Characteristics

# ML2031VRC10-WE

## Medilec, Residual Current Circuit Breaker, 2 Pole, 20A, 10mA, Vertical



### Main

Product or component type	Residual current device
Product brand	Clipsal
Poles description	2P
[In] rated current	20 A
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type I

### Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC
Mounting mode	Flush mounting
Size	116 x 76 mm conforming to DIN 43880
Colour	White electric
Number of gangs	1 gang

### Environment

Standards	AS/NZS 3190
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	9.4 cm
Package 1 Length	12.0 cm
Package 1 Weight	210.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>