


## Product data sheet

### Characteristics

# MX9B321N

## Clipsal MAX9, MAXBAR Top Feed, 3P+N, 21 Modules, 100 A with N Block and Accessories



### Main

Product brand	Clipsal
Range	MAX9
Product or component type	Comb busbar
Total number of 18 mm modules	21

### Complementary

Number of ways	Outgoer: 17 ways N + L Incomer: 4 ways N + 3 L
Poles configuration	Outgoer: 3P + N
Connection pitch	Incomer: 18 mm Outgoer: 9 mm
Insulation	Insulated
Device presentation	Cuttable
Provided components	2 end-pieces 6 tooth covers 1 connector 1 neutral terminal block
[Ie] rated operational current	100 A
[Ue] rated operational voltage	400 V AC
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	4 kV
Mounting mode	Horizontal
Mounting location	Top
Colour	White (RAL 9003)

### Environment

Standards	AS/NZS 61439-3 AS/NZS 3000
Fire resistance	960 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	40.0 cm
Package 1 Length	12.5 cm
Package 1 Weight	363.0 g
Unit Type of Package 2	CAR

Number of Units in Package 2	10
Package 2 Height	26.5 cm
Package 2 Width	24.6 cm
Package 2 Length	40.2 cm
Package 2 Weight	4.0 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	7-year
----------	--------