

## Product data sheet

### Characteristics

# MX9E2315S

Clipsal MAX9, Switchboard Enclosure, Type 2, 3 Row, 45 Ways, Surface Mount



### Main

|                                 |   |
|---------------------------------|---|
| Range                           | MAX9  |
| Product brand                   | Clipsal   |
| Product or component type       | Enclosure   |
| Device application              | Distribution  |
| Number of 18 mm modules per row | 15  |
| Provided equipment              | Earthing bar<br>Neutral bar<br>Circuit identification label<br>Blanking plate |
| Colour                          | White electric (RAL 9003)   |
| Door type                       | Plain door - right and left   |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Enclosure mounting             | Surface                 |
| Number of horizontal rows      | 3                       |
| [Ue] rated operational voltage | 240/415 V AC            |
| [In] rated current             | 100 A                   |
| [Ui] rated insulation voltage  | 500 V                   |
| Number of ways                 | 45 ways                 |
| Cable entry                    | Knock-out cable entries |
| Type of rail                   | DIN                     |
| Enclosure material             | Housing: metal          |
| Width                          | 376 mm                  |
| Height                         | 666 mm                  |
| Depth                          | 120 mm                  |

### Environment

|                         |                               |
|-------------------------|-------------------------------|
| Standards               | AS/NZS 61439-3<br>AS/NZS 3000 |
| Fire resistance         | 650 °C                        |
| IP degree of protection | IP40                          |
| IK degree of protection | IK05                          |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 12.2 cm  |
| Package 1 Width              | 38.2 cm  |
| Package 1 Length             | 68.5 cm  |
| Package 1 Weight             | 6.038 kg |
| Unit Type of Package 2       | P12      |
| Number of Units in Package 2 | 50       |

|                  |          |
|------------------|----------|
| Package 2 Height | 210.0 cm |
| Package 2 Width  | 80.0 cm  |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 320.0 kg |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

### Contractual warranty

|          |        |
|----------|--------|
| Warranty | 7-year |
|----------|--------|