

## Product data sheet

### Characteristics

# NSYBRF12PLAG

Thalassa, 19" fixed chassis 12U for PLA enclosure H750xW750mm



### Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	19" & nbsp; rack
Application	Multi-purpose
For enclosure nominal dimensions	-
Rack type	Fixed
Mounting location	Front of enclosure
Range compatibility	Thalassa (Thalassa PLA) Thalassa (Thalassa PHD)
Device composition	Fixing elements 2 19" uprights
Quantity per set	Set of 1
Number of units 19"	12

### Complementary

Material	Sheet steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Fixing mode	By fixing element
Permanent permissible load	3 kg per unit
Height	750 mm nominal:
Thickness	2 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	79.5 cm
Package 1 Width	11.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	3.857 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information

 [Yes](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---