

Product data sheet

Characteristics

NSYCAG130X110LM

ClimaSys, Metal outlet grille cut-out 104x80mm ext dim 120x120mm IP23



Main

Range	ClimaSys
Product	ClimaSys CA
Product or component type	Metal louvre plate
Accessory / separate part categor	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting location	Sides of enclosure
Fixing mode	By screws
Device composition	1 metal louvre

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Cut-out dimensions	110 x 130 mm
Height	External: 160 mm
Width	External: 160 mm
IP degree of protection	IP23

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	16.000 cm
Package 1 Length	16.000 cm
Package 1 Weight	301.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.450 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	87.600 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------