

## Product data sheet

### Characteristics

# NSYCAG170X190LM

ClimaSys, Metal outlet grille cut-out 104x80mm  
ext dim 120x120mm IP23



### Main

Range	ClimaSys
Product	ClimaSys CA
Product or component type	Metal louvre plate
Accessory / separate part category	Thermal management accessory
Accessory / separate part destination	ClimaSys ventilation system
Mounting location	Sides of enclosure
Fixing mode	By screws
Device composition	1 metal louvre

### Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Cut-out dimensions	170 x 190 mm
Height	220 mm external:
Width	220 mm external:
IP degree of protection	IP23

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	22 cm
Package 1 Length	22 cm
Package 1 Weight	617 g
Unit Type of Package 2	CAR
Number of Units in Package 2	15
Package 2 Height	20 cm
Package 2 Width	40 cm
Package 2 Length	30 cm
Package 2 Weight	10.04 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	720
Package 3 Height	122.5 cm
Package 3 Width	110.5 cm
Package 3 Length	123 cm
Package 3 Weight	493.92 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------