

## Product data sheet

### Characteristics

# NSYCR150WU2C

## ClimaSys, ClimaSys PTC heating resistance 150W, 110-250V insulate



### Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	150 W
Input voltage	110...250 V AC 50/60 Hz
Electrical connection	4 screw terminals 2.5 mm <sup>2</sup>

### Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	VDE[RETURN]UL
Material	Body: extruded aluminium Cover: plastic
Height	150 mm external:
Width	60 mm external:
Depth	90 mm external:
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	10.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	492.0 g
Unit Type of Package 2	P12
Number of Units in Package 2	500
Package 2 Height	120 cm
Package 2 Width	80 cm
Package 2 Length	105 cm
Package 2 Weight	289 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------