

Product data sheet

Characteristics

NSYDLM24

Spacial, Modular chassis DLM type for SPACIAL WM enclosure, 24 modules, H400xW300mm



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Application	Modular distribution application Multi-purpose
Product or component type	Chassis
Device short name	DLM
For enclosure nominal dimensions	-
Mounting location	Front of enclosure Step slide
Range compatibility	Spacial (Spacial S3D) Spacial (Spacial S3X) Spacial (Spacial CRN)
Device composition	1 chassis structure 2 finish cover 1 neutral/earth strip 2 x 16 mm ² 5 x 6 mm ² 2 front panels with 35 mm DIN rail
Quantity per set	Set of 1

Complementary

Material	Steel
Colour	Front panel: grey (RAL 7035)
Surface finish	Polyester powder
Fixing mode	By fixing element - on front and back with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number of horizontal rows	2
Total number of 18 mm modules	24
Type of front plate	Plain and cut-out plates
Number of cut-out	2 cut-outs
Height	353 mm
Width	255 mm
Depth	101.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	27.0 cm
Package 1 Length	36.5 cm
Package 1 Weight	2.548 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------