

## Product data sheet

### Characteristics

# NSYPAP43G

## reversible internal door polyester 2 locks grid pattern for PLM43



### Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Front side
Range compatibility	Thalassa PLM
Device composition	1 door 1 handle 4 fixing brackets



### Complementary

Material	Polyester charged with fibreglass
Colour	Grey (RAL 7035)
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening side	Reversible (110 °)
Height	315 mm grid pattern:
Width	205 mm grid pattern:
Depth	26 Mm available depth between enclosure door: 152 mm available depth between rear:

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	960.0 g
Package 1 Height	4.3 cm
Package 1 width	27.5 cm
Package 1 Length	39.5 cm

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>