

Product data sheet

Characteristics

NSYS3D3215P

Spacial, Wall mounted steel enclosure,
Spacial S3D, plain door, with mounting plate,
300x200x150mm, IP66, IK10



Main

| | |
|-----------------------------|---|
| Range | Spacial |
| Product name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure nominal height | 300 mm |
| Enclosure nominal width | 200 mm |
| Enclosure nominal depth | 150 mm |
| Door type | Plain |
| Mounting plate description | Plain |
| Type of gland plate | Standard |
| Installation accessory type | Wall-mounting |
| Device composition | 1 body 1 mounting plate 1 door with lock 1 cable gland plate |

Complementary

| | |
|-----------------------------|---|
| Body type | Single piece body Gutter-shaped front rail double sheet thickness |
| Number of doors | Front face: 1 door(s) |
| Door opening side | Reversible (120 °) |
| Lock type | 3 mm double-bar lock |
| Accessibility for operation | Front |
| Removable parts | Door by hinges Cable gland plate by screws Mounting plate by fixing element |
| Material | Enclosure: steel Mounting plate: galvanised steel |
| Surface finish | Enclosure: epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) |
| Standards | IEC 62208 |
| Product certifications | LR UL BV GL DNV cUL |
| Net weight | 3.58 kg |

Environment

| | |
|---------------------------|------------------------------|
| NEMA degree of protection | NEMA 4X/13 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| IP degree of protection | IP66 conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 19.5 cm |
| Package 1 Width | 21.0 cm |
| Package 1 Length | 31.5 cm |
| Package 1 Weight | 3.602 kg |
| Unit Type of Package 2 | PAM |
| Number of Units in Package 2 | 105 |
| Package 2 Height | 170.0 cm |
| Package 2 Width | 100.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 381.0 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|