

Product data sheet

Characteristics

NSYS3X101030

Spacial, Wall mounted enclosure, Spacial S3X, stainless steel 304L, double plain door, 1000x1000x300mm, IP55



Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	1000 mm
Nominal width	1000 mm
Nominal depth	300 mm
Product installation	Wall-mounting
Device composition	1 body 2 door 1 lock: door 1 reinforcement frame drilled: door

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	Reversible (120 °)
Lock type	3 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	47 kg

Environment

Standards	IEC 62208
Product certifications	CAN/CSA 22[RETURN]UL 508 type A
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Specific hygiene Corrosive

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	101.0 cm
Package 1 Width	101.0 cm
Package 1 Length	31.0 cm
Package 1 Weight	47.0 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	3
Package 2 Height	120 cm
Package 2 Width	125 cm
Package 2 Length	115 cm
Package 2 Weight	156 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------