

## Product data sheet

### Characteristics

# NSYTBP11116

PC box IP66 IK08 RAL7035 Int.H105W105D55  
Ext.H116W116D62 opaque PC cover H10



#### Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	116 mm
Width	116 mm
Depth	62 mm
Internal height	105 mm
Internal width	105 mm
Internal depth	55 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 5
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

#### Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	TÜV UL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Net weight	0.171 kg

#### Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	171.0 g
Package 1 Height	12.2 cm
Package 1 width	12 cm
Package 1 Length	33 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	857.0 g
Package 2 Height	12.2 cm
Package 2 width	12 cm
Package 2 Length	33 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	75
Package 3 Weight	14.66 kg
Package 3 Height	40 cm
Package 3 width	40 cm
Package 3 Length	60 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------