

Product data sheet

Characteristics

NSYTRAC162

Linery, Cover plate, Linery TR, 2 points, 2.2mm width, for screw terminal NSYTRV162, grey, Set of 50



Main

Range	Linery
Product name	Linery TR
Product or component type	Cover plate
Device short name	TRA
Accessory / separate part categor	Insulation accessory
Product compatibility	TRV screw terminal - passthrough terminal block, length = 55.5 mm TRV screw terminal - protective earth terminal block, length = 55.5 mm
Thickness	2.2 mm

Complementary

Cable cross section	16 mm ²
Number of connections	2
Number of measurement input	2
Quantity per set	Set of 50
Net weight	3.5 g
Colour	Grey

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.500 cm
Package 1 Width	5.000 cm
Package 1 Length	5.500 cm
Package 1 Weight	3.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	4.000 cm
Package 2 Width	17.000 cm
Package 2 Length	17.000 cm
Package 2 Weight	179.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	1600
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.224 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------