

Product data sheet

Characteristics

NSYTRAC22

Linery, Cover plate, Linergy TR, 2 points,
2.2mm width, for screw terminals NSY
TRV22,TRV42,TRV, grey, Set of 50



Main

Range	Linery
Product name	Linery TR
Product or component type	Cover plate
Device short name	TRA
Accessory / separate part category	Insulation accessory
Product compatibility	TRV screw terminal - passthrough terminal block, length = 47.7 mm TRV screw terminal - protective earth terminal block, length = 47.7 mm TRV screw terminal - blade disconnect terminal block, length = 55 mm
Thickness	2.2 mm

Complementary

Cable cross section	6 Mm ² 2.5 Mm ² 4 Mm ² 10 mm ²
Number of connections	2
Number of measurement input	2 1
Quantity per set	Set of 50
Net weight	2.4 g
Colour	Grey

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	4.000 cm
Package 1 Length	4.700 cm
Package 1 Weight	2.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	3.000 cm
Package 2 Width	13.000 cm
Package 2 Length	17.000 cm
Package 2 Weight	127.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	3600
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.950 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------