

## Product data sheet

### Characteristics

# NSYTRAL25

Linery, Plug-in bridge, Linery TR, 5 points, for 2.5mm<sup>2</sup> terminal blocks, red, 5 ways, set of 50



### Main

Range	Linery
Product name	Linery TR
Product or component type	Plug-in bridge
Device short name	TRA
Accessory / separate part categor	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	5 ways

### Complementary

Cable cross section	2.5 mm <sup>2</sup>
Number of connections	2 4 3
Number of measurement input	1 4 2 6 3
Quantity per set	Set of 50
Net weight	4.2 g
Colour	Red

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8 cm
Package 1 Length	14 cm
Package 1 Weight	4 g
Unit Type of Package 2	BAG
Number of Units in Package 2	50
Package 2 Height	2.5 cm
Package 2 Width	8 cm
Package 2 Length	14 cm
Package 2 Weight	212 g
Unit Type of Package 3	S01
Number of Units in Package 3	1000
Package 3 Height	15 cm
Package 3 Width	15 cm

Package 3 Length	40 cm
Package 3 Weight	4.406 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

### Contractual warranty

Warranty	18 months
----------	-----------