

Product data sheet

Characteristics

O3015-BK

Clipsal Iconic Outdoor, Single, Switched socket outlet, horizontal, 10A, 250V



Main

Range of product	Iconic
Product or component type	Switched socket
Product brand	Clipsal
Device presentation	Complete product
Switch application	On/off switching
Outlet poles configuration	1P + E

Complementary

Control type	ON/OFF button Rocker
Pin number	3
Number of power socket outlets	1
Socket-outlet type	Single socket-outlet
Fixing mode	By screws By clipping locks
Local signalling	Without light indicator
Device mounting	Surface Wall mounted
Mounting position	Horizontal
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Surface finish	Matt
Type of installation	Outdoor
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
[In] rated current	10 A
Clamping connection capacity	3 x 2.5 mm ² 2 x 4 mm ²
Connections - terminals	3 screw terminals
Depth	70 mm
Height	85 mm
Width	115.5 mm

Environment

IP degree of protection	IP54
Product certifications	RCM
Electrical durability	12000 cycles
Ambient air temperature for storage	0...60 °C
Standards	AS/NZS 3112
Relative humidity	10...95 %
Ambient air temperature for operation	0...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	11.9 cm
Package 1 Length	8.9 cm
Package 1 Weight	274.0 g
Unit Type of Package 2	BB2
Number of Units in Package 2	30
Package 2 Height	30.9 cm
Package 2 Width	41.3 cm
Package 2 Length	45.9 cm
Package 2 Weight	9.22 kg
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	119.14 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Halogen content performance	Halogen free plastic parts product