

Product data sheet

Characteristics

O3015T-XW

Clipsal Iconic Outdoor, Single, Switched socket outlet, with timer, 10A, 250V



Main

Range of product	Iconic
Product or component type	Switched socket
Product brand	Clipsal
Device presentation	Complete product
Software name	Wiser by SE App
Switch application	On/off switching
Technology type	Bluetooth low energy Zigbee
Memory description	Backup memory Backup memory
Memory usage	Date and time Program
Outlet poles configuration	1P + E

Complementary

Control type	ON/OFF button Rocker By mobile application
Pin number	3
Number of power socket outlets	1
Socket-outlet type	Single socket-outlet
Fixing mode	By screws By clipping locks
Local signalling	Without light indicator
Device mounting	Surface Wall mounted
Mounting position	Horizontal
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Surface finish	Matt
Type of installation	Outdoor
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
[In] rated current	10 A
Clamping connection capacity	3 x 2.5 mm ² 2 x 4 mm ²
Connections - terminals	3 screw terminals
Depth	82 mm
Height	85 mm
Width	115.5 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP54
Product certifications	RCM
Electrical durability	12000 cycles
Standards application	Safety Safety EMC Radio
Ambient air temperature for storage	0...60 °C
Standards	AS/NZS 3112
Relative humidity	10...95 %
Ambient air temperature for operation	0...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.1 cm
Package 1 Width	11.9 cm
Package 1 Length	8.9 cm
Package 1 Weight	332.0 g
Unit Type of Package 2	BB2
Number of Units in Package 2	25
Package 2 Height	33.5 cm
Package 2 Width	26.1 cm
Package 2 Length	45.9 cm
Package 2 Weight	9.3 kg
Unit Type of Package 3	P06
Number of Units in Package 3	300
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	120.1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product