

Product data sheet

Characteristics

O3025-XW

Switched socket outlet, Iconic Outdoor, horizontal, Twin, 10 A, 250 V, Extra white



Main

Range of product	Iconic
Product or component type	Switched socket
Product brand	Clipsal
Device presentation	Complete product
Colour	White
Colour code	XW
Switch application	On/off switching
Outlet poles configuration	1P + E

Complementary

Control type	ON/OFF button Rocker
Pin number	6
Number of power socket outlets	2
Socket-outlet type	Twin switched socket-outlet
Fixing mode	By screws By clipping locks
Local signalling	Without light indicator
Device mounting	Surface Wall mounted
Mounting position	Horizontal
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Surface finish	Matt
Type of installation	Outdoor
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
[In] rated current	10 A
Clamping connection capacity	4 x 2.5 mm ² 3 x 4 mm ²
Connections - terminals	3 screw terminals
Depth	70 mm
Height	85 mm
Width	115.5 mm

Environment

IP degree of protection	IP54
Product certifications	RCM
Electrical durability	12000 cycles
Ambient air temperature for storage	0...60 °C
Standards	AS/NZS 3112
Relative humidity	10...95 %
Ambient air temperature for operation	0...45 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	222.0 g
Package 1 Height	8.7 cm
Package 1 width	11.9 cm
Package 1 Length	8.9 cm
Unit Type of Package 2	BB2
Number of Units in Package 2	30
Package 2 Weight	7.66 kg
Package 2 Height	30.9 cm
Package 2 width	41.3 cm
Package 2 Length	45.9 cm
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Weight	100.42 kg
Package 3 Height	105 cm
Package 3 width	60 cm
Package 3 Length	80 cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free plastic parts product