

Product data sheet

Characteristics

O3041HA-XW

Clipsal Iconic Outdoor, 1 Gang, Switch, horizontal, 20A/16AX 250V



Main

Range of product	Iconic
Range	Iconic
Product brand	Clipsal
Product or component type	Switch
Device presentation	Complete product
Device application	Lighting
Colour	White (XW)
Plug, socket category	Low voltage
Outlet standard	Australian

Complementary

Switch function	1-pole 1/2-way
[Ue] rated operational voltage	230/240 V
Number of rocker	1
Number of poles	1
Number of gangs	1 gang
Device mounting	Surface
Mounting position	Horizontal
Mounting support	Wall
Fixing mode	By screws By clipping locks
Connections - terminals	Screw terminals 4 x 1.5 mm ² 2 x 2.5 mm ²
Material	PC (polycarbonate) TPE (thermoplastic elastomer) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Surface finish	Matt
Installation direction	Horizontal
Surface treatment	Untreated
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	20 A at 230/240 V AC 16 AX at 230/240 V AC
Clamping connection capacity	4 x 1.5 mm ² 3 x 2.5 mm ²
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Wire stripping length	10 mm
Protection type	Without protection
Marking	Without marking
Height	85 mm
Width	115.5 mm
Depth	70 mm
Net weight	0.19 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Targeted country	Australia
Actuator	Rocker

Environment

Ambient air temperature for operation	0...45 °C
IP degree of protection	IP56
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Electrical durability	12000 cycles
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	11.9 cm
Package 1 Length	8.9 cm
Package 1 Weight	274.0 g
Unit Type of Package 2	BB2
Number of Units in Package 2	30
Package 2 Height	30.9 cm
Package 2 Width	41.3 cm
Package 2 Length	45.9 cm
Package 2 Weight	9.22 kg
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	119.14 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Halogen content performance	Halogen free plastic parts product