

## Product data sheet

### Characteristics

# P3015-4C-XW

Clipsal Pro Series, Quad Power Point Skin,  
Horizontal Mount, 250V, 10A, Clip-On



### Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	White (XW)
Type of packing	Polybag

### Complementary

Range compatibility	Pro Series switched socket
Product destination	Switched socket
Number of rocker	4
Number of power socket outlets	4
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Glossy
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin
Height	78 mm
Width	212 mm
Depth	9 mm
Net weight	0.032 kg


### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	7.8 cm
Package 1 Length	21.2 cm
Package 1 Weight	39.05 g

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations