

Product data sheet

Characteristics

P3019-XW

Pro Series, time switch, vertical, 10 A, White



Main

Range	Pro Series
Product or component type	Time switch
Device application	Lighting
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 5

Complementary

Device presentation	Complete product
Control type	Push type
Device mounting	Wall
Installation direction	Vertical
Switch function	1-pole 1-way
Number of rocker	1
Rated current	6 AX
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Height	116 mm
Width	78 mm
Depth	38 mm
Net weight	0.108 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	53.53 g