

Product data sheet

Characteristics

P3025C-XW

Clipsal Pro Series, Twin Power Point Skin, Horizontal Mount, 250V, 10A, Clip-On



Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	White (XW)
Type of packing	Polybag

Complementary

Range compatibility	Pro Series switched socket
Product destination	Switched socket
Number of rocker	2
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Horizontal
Fixing mode	Clip-on
Surface finish	Glossy
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin
Height	78 mm
Width	116 mm
Depth	9 mm
Net weight	0.018 kg


Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.9 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	19.94 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations