

Product data sheet

Characteristics

P3025VC-BK

Pro Series, cover frame, 2 switches & 2 sockets, 10 A, vertical, Black



Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	Black (BK)
Type of packing	Polybag

Complementary

Range compatibility	Switched socket
Product destination	Switched socket
Number of rocker	2
Number of power socket outlets	2
[In] rated current	10 A
Installation direction	Vertical
Fixing mode	Clip-on
Surface finish	Glossy
Material	PC (polycarbonate): window ABS (acrylonitrile butadiene-styrene): skin
Height	116 mm
Width	78 mm
Depth	9 mm
Net weight	0.018 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	19.94 g
Package 1 Height	0.9 cm
Package 1 width	7.8 cm
Package 1 Length	11.6 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile