

Product data sheet

Characteristics

P3041D45-XW

Clipsal Pro Series, Cooking Appliance Isolator Switch, Horizontal/Vertical Mount Double Pole 250V, 45A



Main

Range	Pro Series
Product or component type	Switch
Device application	Cooker
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 5

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Wall
Installation direction	Horizontal/vertical
Switch function	2-pole 1-way
Number of rocker	1
Rated current	45 A
[Ue] rated operational voltage	250 V
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene) POM (polyoxymethylene)
Fixing mode	By screws
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Height	116 mm
Width	78 mm
Depth	38 mm
Net weight	0.096 kg

Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	99.53 g