

Product data sheet

Characteristics

P3041VH-XW

Clipsal Pro Series Gridplate and Skin, 1 Gang, Vertical/Horizontal Mount



Main

Colour tint	White (XW)
-------------	------------

Complementary

Device composition	Fixing frame
Installation direction	Vertical
Number of gangs	1 gang
Surface finish	Glossy
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene)
Height	116 mm
Width	78 mm
Depth	9 mm




Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	97.53 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
