

## Product data sheet

### Characteristics

# P3043HUSB-XW

## Clipsal Pro Series, USB Charging Station, 3 Outlet Type A



### Main

Range	Pro Series
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	3 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	4.5 A

### Complementary

Device mounting	Flush
Device presentation	Complete product
Colour tint	White (XW)
Surface finish	Matt Textured
Fixing mode	By screws
Type of packing	Polybag
Quantity per set	Set of 5
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	-5...50 °C
Relative humidity	10...95 %
Material	PC (polycarbonate) PP (polypropylene) ABS (acrylonitrile butadiene-styrene)
Protection type	Short time short-circuit protection
Number of terminals	3 screw terminal
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 4 mm <sup>2</sup> for rigid or stranded cable(s)
Wire stripping length	16 mm
Standards	AS/NZ 3112
Height	78 mm
Width	38 mm
Depth	38 mm
Embedding depth	35 mm
Net weight	0.094 kg

### Environment

Product certifications	RCM
Electrical insulation class	Class II
IK degree of protection	IK08
IP degree of protection	IP21

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	102.53 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>