

Product data sheet

Characteristics

P3044VH-XW

Clipsal Pro Series, Gridplate and Skin, 4 Gang, Vertical/Horizontal Mount



Main

Range	Pro Series
Product or component type	Cover frame
Colour tint	White (XW)

Complementary

Range compatibility	Pro Series
Device composition	Fixing frame
Installation direction	Vertical
Number of gangs	4 gangs
Surface finish	Glossy
Material	PC (polycarbonate) ABS (acrylonitrile butadiene-styrene)
Height	116 mm
Width	78 mm
Depth	9 mm

Environment



Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	7.8 cm
Package 1 Length	11.6 cm
Package 1 Weight	97.53 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
