

Product data sheet

Characteristics

P3046VH-XW

Clipsal Pro Series, Gridplate and Skin, 6 Gang, Vertical/Horizontal Mount



Main

| | |
|---------------------------|-------------|
| Range | Pro Series |
| Product or component type | Cover frame |
| Colour tint | White (XW) |

Complementary

| | |
|------------------------|---|
| Range compatibility | Pro Series |
| Device composition | Fixing frame |
| Installation direction | Vertical |
| Number of gangs | 6 gangs |
| Surface finish | Glossy |
| Material | PC (polycarbonate) ABS (acrylonitrile butadiene-styrene) |
| Height | 116 mm |
| Width | 78 mm |
| Depth | 9 mm |




Environment

| | |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...45 °C |
| Relative humidity | 10...95 % |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 7.8 cm |
| Package 1 Length | 11.6 cm |
| Package 1 Weight | 97.53 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

| | |
|--------------------------|--|
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |