

Product data sheet

Characteristics

P3JH900AL-WE

Airflow, Ceiling Sweep Fan 3 Aluminium Blades
900mm



Main

Range	Clipsal
Product brand	Clipsal
Device short name	sweep fan
Product or component type	Fan
Product destination	Ceiling fan
Device application	Residential Commercial

Complementary

Provided equipment	Fan 900 mm
[Ue] rated operational voltage	240 V AC 50 Hz
Material	Aluminium
Air flow	8340 m3/h
Power consumption in W	60 W
Maximum revolution speed	375 rpm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	26.5 cm
Package 1 Length	41.5 cm
Package 1 Weight	5.5 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	3 Years
----------	---------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.