

## Product data sheet

### Characteristics

# P40MBPR-XW

Clipsal Pro Series, Switch Mechanism, Bell Press Return, 250V, 10A



### Main

Range	Pro Series
Product or component type	Switch
Device application	Momentary switch
Colour tint	White
Type of packing	Polybag
Quantity per set	Set of 20

### Complementary

Device presentation	Mechanism with central plate
Control type	Rocker
Switch function	1-pole 1/2-way
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Material	PC (polycarbonate) PA66 ABS (acrylonitrile butadiene-styrene)
Fixing mode	By clips
Surface finish	Glossy
Surface treatment	Untreated
Connections - terminals	Screw terminal
Clamping connection capacity	1 x 1.5...4 x 1.5 mm <sup>2</sup> for rigid or stranded cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s)
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

### Environment

Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Product certifications	RCM

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.2 cm
Package 1 Length	2.4 cm
Package 1 Weight	16.98 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>